

Portable HEPA System Series - PHS

TECHNICAL INFORMATION

In the interest of continuing product improvement, we reserve the right to change models, specifications, and/or features without prejudice.

PROJECT:		
LOCATION:		
ARCHITECT:		
ENGINEER:		
CONTRACTOR:		
DATE:	SALES ENGINEER:	

Page: CF-9

www.monoxivent.com

info@monoxivent.com


309-794-1000

PORTABLE HEPA SYSTEM SERIES - PHS

The Monoxivent portable filter unit is used mainly for source capture and extraction of welding smoke. Different filter combinations allow the PHS to evolve into a more versatile unit.

The contaminated air is drawn into the top of the cabinet by an arm or central duct attached to the top.

The particulate passes through a first stage poly pre-filter. Large particles are trapped in the pre-filter. The standard main filter (99% HEPA) then captures and removes the very smallest of smoke particles. If desired, a third stage filter is supplied. The third stage filter is usually a carbon cell, which is used for the removal of odors.



The poly pre-filter is supplied with a reusable frame, in which only the poly material is removed, discarded, and replaced.

